



Locking Devices, Twist-Lock®, Marine Grade, Male Plug, 15A 125V, 2-Pole 3-Wire Grounding, L5-15P, Screw Terminal, Yellow

By Hubbell Wiring Device-Kellems
Catalog # [HBL47CM20C](#)



Locking Devices, Twist-Lock®, Marine Grade, Male Insulgrip® Plug, 15A 125V, 2-Pole 3-Wire Grounding, NEMA L5-15P, Screw Terminal, Corrosion Resistant, Yellow.

Features

- Individually molded face for each blade configuration
- Roomy wiring chamber provides ample space for wiring
- Ribbed nylon housing provides a secure grip that's impact and chemical resistant

Application

Extra Heavy Duty Industrial

General

Color	Yellow, White
Cord Range	0.230"-0.720"(5.8-18.3)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	15A Corrosion Resistant Insulgrip® Plug
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - HB or better per UL94 or CSA 22.2 No. 0.6 • Environmental - Moisture Resistance - IP20 Suitability • Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact) • Mechanical - Terminal Accommodation - #18 AWG - #10 AWG stranded

Electrical Ratings

Amperage Rating	15 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Cable Range	0.230 - 0.720 in
Cord Type	All Listed Portables
Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed.Spec. W-C-596 • Listed to UL 498
----------------------	---

Nema Rating	L5-15P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK AA-36 Catalog Page](#)
- [Catalog Page - WDK B-12 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL47CM20C AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2437_INSTALLINST](#)
- [Literature - Safety Product Guide](#)
- [Literature - Food Processing Guide](#)
- [Literature - Hubbell Marine Full Line Catalog](#)
- [Sales Drawings - WDK_HBL47CM_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Marine Electrical Products](#)
- [Video - Insulgrip Twist-Lock and Straight Blade Devices](#)
- [Video - Twist-Lock Devices](#)

AWG and AWG stranded
copper wire only.

Related Products

Type	<ul style="list-style-type: none">Mechanical - Terminal Identification - Terminals identified in accordance with UL 498PlugsPlugs
UPC	783585160504

HBL47CM29C - Locking Devices, Twist-Lock®, Marine Grade, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Yellow

HBL60CM23 - Twist-Lock® Devices, 20A Accessories, Weatherproof Boot, Seal-Tite® triple seal cover for connector bodies when used in cord sets, Yellow

HBL47CM00 - Locking Devices, Twist-Lock®, Marine Grade, Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Yellow

Dimensions

Dimensions	1.53 in x 1.53 in x 1.97 in
Display Size	Standard Sized
Height	1.97 in
Length	1.53 in
Weight	0.05 lb
Width	1.53 in



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL47CM20C-SPEC-EN | REV 1/2024