



Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Male, Flanged Inlet, 100A 3-Phase Wye 120/208V AC, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [HBL5100B9W](#)



Heavy Duty IEC Pin and Sleeve Industrial Grade Male Flanged Inlet, 100A 3-Phase Wye 120/208V AC, 4-Pole 5-Wire Grounding, Terminal Screws, Watertight.

Features

- Solid one-piece pins for reliable electrical contact
- Gasketed sealing ring provides watertight seal
- Raised collar surrounds each phase pin

Application

High Ampacity Watertight Connections

General

Color	<ul style="list-style-type: none"> • Blue • Bleu
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	Single Flanged
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstand 3000V AC • Electrical - Max. Working Voltage - 600V RMS • Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17 • Environmental - Ingress Protection - IP67 Suitability • Environmental - Moisture Resistance - Watertight per IEC 60309-1 • Environmental - Operating Temperatures - Maximum Continuous 75°C • Minimum - 40°C w/o impact • Mechanical - Impact Resistance - Per CSA C22.2

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating	100 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	100 A
Current Rating	100 A
Dielectric Strength	Withstands 3000V Minimum in
Phase	Three Phase
Voltage Rating	3 Phase Y 120/208 VAC
Voltage Rating Description	3 Phase Y 120/208 VAC
Wattage	20800

Conductor Related

Number Of Wires	5-Wire
Wire Size	#3 AWG to #1/0 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified File LR280C • UL Classified to IEC 60309-1 IEC 60309-2 • UL Listed, File E146032
----------------------	--

Nema Rating Non-NEMA

Logistics

Carton Quantity 6

Product Assets

[Catalog Page - WDK G-11 Catalog Page](#)
[Catalog Page - WDK G-7 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - HBL5100B9W AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1304_INSTALLINST Literature - IEC Pin & Sleeve Devices](#)
[Literature - Advantage™ Series Switch-Rated IEC Pin & Sleeve Devices](#)
[Literature - Dual-Certified IEC Pin & Sleeve Devices](#)
[Sales Drawings - WDK_HBL5100B_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

No. 182.1 / UL1682

- Mechanical - Product Identification - Ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

Series	HBL Heavy Duty
Style	Standard Service
Temperature Rating	Maximum continu : 75° C ; Minimum continu : -40° C sans impact
Type	<ul style="list-style-type: none">• Watertight Inlet• Watertight Inlet
UPC	783585405032



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL5100B9W-SPEC-EN | REV 1/2024