

IEC Pin and Sleeve Devices, Industrial Grade, Female, Receptacle, 125A 380/415V, 4-Pole 5- Wire Grounding, Terminal Screws, Red, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [HBL5125R6W](#)

Heavy Duty IEC Pin and Sleeve Industrial Grade Female Receptacle, 125A 380/415V, 4-Pole 5-Wire Grounding, Terminal Screws, Watertight.

Features

- Self-closing gasketed cover
- Color coded housings for easy identification
- Super tough insulated non-metallic housing

Application

High Ampacity Watertight Connections

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstand 3000V AC
- Electrical - Max. Working Voltage - 600V RMS
- Environmental - Flammability - HB or better per UL 94 or CSA C22.2 No. 0.17
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Moisture Resistance - Watertight per IEC 60309-1
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum - 40°C w/o impact
- Mechanical - Impact Resistance - Per CSA C22.2 No. 182.1 / UL1682
- Mechanical - Product Identification - Ratings are a permanent part of the device housing
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and IEC conventions

General

Catalog Number	HBL5125R6W
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Item Type	Single Flanged
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	4-Pole
Series	HBL Heavy Duty



Specifications

Style	Standard Service
Type	Watertight Receptacle
UPC	783585405162

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	125 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	125 A
Current Rating	125 A
Phase	Three Phase
Voltage Rating	<ul style="list-style-type: none">• 220/380 V V V• 240/415 V V V
Voltage Rating Description	220/380 V;240/415 V
Wattage	51875

Conductor Related

Number Of Wires	5-Wire
Wire Size	#3 AWG to #1/0 AWG

Certifications And Compliance

Industry Standard(s)	Listed To Standard UL1682
Nema Rating	Non-NEMA

Logistics

Carton Quantity	6
-----------------	---

Product Assets

Catalogs - WDK Catalog Full 2024

Engineering Drawing - HBL5125R6W AutoCAD Drawing

Installation Manuals - WIRING_PD1309_INSTALLINST

Literature - PULP & PAPER SOLUTIONS

Literature - Pulp & Paper Solutions

Sales Drawings - WDK_HBL5125R6W_DRAWING_PDF

Specifications - HBL5125R6W Specification Sheet French

Specifications - Wiring HBL5125R6W Specification Sheet

Warranty - Industrial & Commercial Products



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_CA-HBL5125R6W-SPEC-EN | REV 10/2024