

Kellems Wire Management, Splicing Grips, Rotating Wire Rope Splicing, 1.00-1.13"

By Hubbell Wiring Device-Kellems
Catalog # [03317004](#)

Kellems Wire Management, Splicing Grips, Rotating Wire Rope Splicing, 1.00-1.13"



Application

Wire Rope Splicing

Performance

- Mechanical - Approximate Breaking Strength - 16,000 (71,168)
- Mechanical - Approximate Strength of Grip per Foot - 8.67 (2.64)
- Mechanical - Barrel Dimensions - 5.50" (13.97) x 1.37" (3.48)
- Mechanical - Working Load - (program formula 5% of Approximate Breaking Strength)

General

Approx Breaking Strength	16,000 lbs
Catalog Number	03317004
Color	Metallic
EU RoHS Indicator	Yes
Environmental Conditions	No Limitations
Material	Steel, Galvanized
Material - Mounting Hardware	On Cable Ends
Series	Wire Rope Grips
Specifications	<ul style="list-style-type: none">• Bushing - Steel• Lug - Steel• Shoulders - Aluminum• Strand - Galvanized Steel

- Swivel - Steel
- Tag - Mylar
- Tube - Steel

Style

Closed Mesh, Triple, Double, Single Weave

Type
UPC

Rotating Wire Rope
783585317243

Dimensions

Display Size

Standard Sized Product

Conductor Related

Cable Diameter Range	1.00 in-1.13 in
Cable Size	1.00"-1.13" (2.54-2.86)
Number of Conductors	1

Certifications And Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 3317004](#)
- [Warranty - Industrial & Commercial Products](#)