

## Kellems Wire Management, Dusttight Grips, Strain Relief, 1.25- 1.50", 1.50", Insulated

By Hubbell Wiring Device-Kellems

Catalog # [073031212](#)

Kellems Wire Management, Dusttight Grips, Strain Relief, 1.2-1.5",  
1.50", Insulated



### General

Application	Light Duty
Approx Breaking Strength	3,000 lbs
Catalog Number	073031212
Color	
Construction	Woven
EU RoHS Indicator	Yes
Item Type	Dust-Tight Strain Relief Grips
Material	Aluminum Fittings, Galvanized Steel Mesh
Material - Mounting Hardware	Locknut or Tapped Hole
Performance	Environmental - Flammability - UL 94HB (Strand grip), UL 94V-2 (Fitting)  Environmental - Hazardous Locations - Suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C
Series	Dust-Tight
Style	For Insulated Cables
Thread Size	1 1/2" NPT
Type	Insulated, Wide Range
UPC	783585330129

### Dimensions

Dimension - Thread Size	1.313" (3.02)
Display Size	Standard Sized
Trade Size	1.5

### Conductor Related

Cable Diameter Range	1.25 in-1.50 in
Cable Size	1.25"-1.50" (3.17-3.81)
Cable Specification	Mesh Length @ Nom. Dia. : 11.75" (29.84 cm)

### Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

### Logistics

Carton Quantity	2
-----------------	---

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Literature - Wire Management Solutions Brochure](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-073031212-SPEC-EN | REV 6/2024