




# Straight Blade Male Plug, Valise Series, Industrial/Commercial, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Orange, Single Pack, Economy Ver

By Hubbell Wiring Device-Kellems  
Catalog # [HBL515PVO](#)



Straight Blade Devices, Male Plug, Valise Series, Industrial/CommercialGrade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Orange, Single Pack, Economy Version.

## Features

- Hinged one piece body design for easy assembly
- Powerful, offsetting cord grips clamp on individual conductors
- Assembly screws are captive and will not fall out while wiring

## Application

Industrial/Commercial Grade

## General

Color	<ul style="list-style-type: none"> <li>• Orange</li> <li>• Orange</li> </ul>
Horsepower - Maximum	0.50
Item Type	Valise
Material	Polycarbonate
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical:Current Interrupting: Certified for current interrupting at full rated current</li> <li>• Dielectric Voltage: Withstands 2,000V minimum</li> <li>• Mechanical: Product Identification: Ratings are a permanent part of the device</li> <li>• Terminal Accommodation: #18-#12 AWG stranded copper wire only</li> <li>• Terminal Identification: Terminals identified in accordance with UL 498 and CSA</li> <li>• Environmental</li> </ul>

## Dimensions

Weight 0.1 lb

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified to C22.2 No 42 File 280C</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed to UL498 File E1706</li> </ul>
Nema Rating	5-15P
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity 50

## Product Assets

[Catalog Page - WDK A-37](#) [Catalog Page Catalogs - WDK Catalog Full 2023](#)  
[Literature - WIRING\\_WLFVM034](#)  
[Literature - Pulp & Paper Solutions](#)  
[Warranty - Industrial & Commercial Products](#)

:Flammability: UL 94 HB or better

- IP Suitability: IP20
- Operating Temperatures:  
Maximum continuous 75°C
- minimum -40°C (w/o impact)

UPC

783585000534



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL515PVO-SPEC-EN | REV 1/2024