



# Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2- Pole 3-Wire Grounding, 15A 125V, 5-15R, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [5252AG](#)



Straight Blade Devices, Receptacles, Duplex,  
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A  
125V, 5-15R, Gray

## Features

- Easy access split circuit tab
- Smooth face
- Triple wipe contacts
- Wrap-around galvanized steel strap

## Application

Hubbell-Pro Heavy Duty

## General

Color	<ul style="list-style-type: none"> <li>• Gray</li> <li>• Gris</li> </ul>
Environmental Conditions	Indoor Dry unless protected by additional means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Thermoplastic/Composite
Material - Mounting Hardware	Screw Mounting
Mounting Type	Screw Mount
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - UL 94 V-2</li> <li>• Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)</li> <li>• Mechanical - Product Identification - Ratings are a permanent part of the device</li> <li>• Mechanical - Terminal</li> </ul>
-------------	--

## Dimensions

Dimensions	3.28 in x 1.41 in x 1.1 in
Display Size	Standard Sized Product
Height	1.1 in
Length	3.28 in
Weight	0.15 lb
Width	1.41 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications and Compliance

Industry Standard(s)	UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant
Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminal wire leads identified in accordance with UL 498

Series	Hubbell-PRO
Size	Standard Sized Product
Style	Smooth Face
Temperature Rating	Maximum continuous 75°C; minimum -40°C (w/o impact)
Type	<ul style="list-style-type: none"><li>• Standard Duplex</li><li>• Standard Duplex</li></ul>
UPC	783585109701



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-5252AG-SPEC-EN | REV 1/2024