

Straight Blade Devices, Receptacles, Duplex, Hubbell-Pro Heavy Duty, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Orange, Single Pack, Isolated Ground.



By Hubbell Wiring Device-Kellems
Catalog # [CR5352IG](#)

Straight Blade Devices, Receptacles, Duplex, Hubbell-Pro Heavy Duty, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Orange, Single Pack, Isolated Ground.

Application

- Hubbell-Pro Heavy Duty

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	CR5352IG
Color	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Hubbell-PRO
Specifications	<ul style="list-style-type: none"> • Automatic Self-grounding Clip - Stainless steel • Base - PBT • Clamp - Nickel plated steel • Face - Nylon

Style
Type
UPC

- Ground Contacts - .031" (.8) Brass
 - Mounting Screws - Stainless Steel
 - Mounting Strap - .040" (1) Galvanized steel
 - Mounting Strap - Galvanized steel
 - Terminal Screws - Brass
- Finder Groove Face
Isolated Ground
783585387802

Dimensions

Dimensions	3.28 in x 1.33 in x 1.05 in
Display Size	Standard Sized Product
Height	1.05 in
Length	3.28 in
Weight	0.22 lb
Width	1.33 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA, C22.2, No. 42 File 285• Fed. Spec. WC596• NEMA® WD-6 Compliant• UL Listed to UL498 File No. E2186
Nema Rating	5-20R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	4000

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Specifications - CR5352IG](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand