

Straight Blade Devices, Extra Heavy
Duty Standard Duplex Receptacles
for Controlled Applications, Fully
Controlled, 15A, 125V,

By Hubbell Wiring Device-Kellems
Catalog # [HBL5262C2TR](#)



Straight Blade Devices,Extra Heavy Duty Standard Duplex
Receptacles for Controlled Applications , Fully Controlled,15A,
125V, 2 Pole, 3 Wire Grounding,Brown

Features

- Permanently marked with universal power symbol and the word "CONTROLLED" to visually identify receptacles used in automatic energy management systems
- Patented TR design eliminates plug-in difficulty and TR complaints
- Markings can be read regardless of mounting orientation
- Complies with NEC Section 406.3, ASHRAE 90.1, and California Title 24 requirements
- Complements Hubbell's Load:Logic® control system or other available energy management system

Application

Extra Heavy Duty Standard Duplex

Performance

- Electrical: Current Interrupting- Certified for current interrupting at full rated current
- Electrical: Dielectric Voltage- Withstands 2,000V minimum
- Mechanical: Product Identification- Ratings are a permanent part of the device
- Mechanical: Terminal Accommodation- #14-10 AWG stranded or solid copper wire only.
- Mechanical: Terminal Identification- Terminals identified in accordance with UL 498 and CSA
- Environmental: Flammability- UL 94V-2
- Environmental: Operating Temperature- Maximum continuous 75°C
- minimum -40°C (w/o impact)

General

Catalog Number	HBL5262C2TR
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Tamper resistant
Item Type	Standard Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Series
Specifications

- Controlled
- Face: Nylon
 - Base: PBT
 - By-Pass Power Contacts : .036 in. (.9) Brass
 - Ground Contacts: .031 in. (.8) Brass
 - Clamping Plate: Plated steel:Mounting Strap: Brass
 - Automatic Self-grounding Staple: Stainless steel
 - Mounting Screws: Zinc plated steel
- Finder Face, Duplex Receptacle
Tamper-Resistant
783585583785

Style
Type
UPC

Dimensions

Display Size	Standard Sized Product
Weight	0.2 lb

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed to UL498 File No. E2186Certified to CSA, C22.2, No. 42 File 285Fed. Spec. W-C-596NEMA® WD-6 Compliant
----------------------	---

Nema Rating 5-15R

Logistics

Carton Quantity 10

Product Assets

Catalog Page - WDK A-24 Catalog Page
Catalogs - WDK Catalog Full 2024

Literature - PULP & PAPER SOLUTIONS
Literature - Pulp & Paper Solutions
Literature - Automatic Receptacle Control Product Guide
Specifications - Wiring HBL5262C2TR Specification Sheet
Specifications - HBL5262C2TR Specification Sheet English
Specifications - HBL5262C2TR
Warranty - Industrial & Commercial Products
Video - Tamper-Resistant Receptacles
Video - Tamper-Resistant Receptacles

