

Straight Blade Devices, Receptacle, Tamper Resistant Decorator Duplex, Commercial Grade, 15A 125V, 2-Pole 3- Wire Grounding, 5-15R, With Night Light

By Hubbell Wiring Device-Kellems
Catalog # [DR15NLIV](#)

Straight Blade Devices, Receptacle, Tamper Resistant Decorator Duplex, Commercial Grade, 15A 125V, 2-Pole 3- Wire Grounding, 5-15R, With Night Light, Ivory.

Application

Commercial Specification Grade

Performance

- Electrical - Color Temperature - 3400K - 3600K
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Electrical - LED Energy Consumed - 0.5 watt
- Electrical - Light Output - 0.5 Lumens
- Electrical - Rating - 15A, 125VAC Only
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	DR15NLIV
Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.5
Item Type	Decorator Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Commercial Specification Grade
Specifications	<ul style="list-style-type: none"> • Automatic Self-grounding Staple - Stainless steel • Base - Nylon • Face - Nylon • Lens - Polycarbonate



- Mounting Screws - Zinc Plated Steel
 - Mounting Strap - Galvanized Steel
 - Power Contacts - .030 in. (.8) Brass
 - Terminal Screws - Plated Steel
 - Wire Clamp - .062 in. (1.6) Nickel plated steel
- Style Line Decorator
Type Nightlight
UPC 783585541310

Style
Type
UPC

Dimensions

Dimensions	3.29 in x 1.15 in x 1.29 in
Display Size	Standard Sized Product
Height	1.29 in
Length	3.29 in
Weight	0.2 lb
Width	1.15 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)

- Certified to CSA, C22.2, No. 42
- NEMA® WD-6 Compliant
- UL Listed to UL498 File No. E2186

Nema Rating

5-15R

Logistics

Carton Quantity

10

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Literature - Residential Catalog](#)

[Specifications - DR15NLIV](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-DR15NLIV-SPEC-EN | REV 10/2024