

**HUBBELL**  
Wiring Device-Kellems

**Straight Blade Devices,  
Receptacles, Duplex,  
Decorator/Commercial/Industrial  
Grade, 2-Pole 3-Wire Grounding,  
15A 125V, 5-15R, White, Single Pack**

By Hubbell Wiring Device-Kellems  
Catalog # [DR15WHI](#)

Straight Blade Devices, Receptacles, Duplex,  
Decorator/Commercial/Industrial Grade, 2-Pole 3-Wire  
Grounding, 15A 125V, 5-15R, White, Single Pack.



## General

Application	Commercial Specification Grade
Catalog Number	DR15WHI
Color	White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Decorator Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current  Electrical - Dielectric Voltage - Withstands 2,000V minimum  Environmental - Flammability - UL 94 V-2  Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)  Mechanical - Product Identification - Ratings are a permanent part of the device  Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only  Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
Series	Commercial Specification Grade
Style Type	Style Line Decorator Standard Duplex  Standard Duplex
UPC	783585127828

## Dimensions

Dimensions	1.29 in x 1.06 in x 3.28 in
Display Size	Standard Sized Product
Height	3.28 in
Length	1.29 in
Weight	0.2 lb
Width	1.06 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	Certified to CSA, C22.2, No. 42 Fed. Spec. W-C-596 NEMA® WD-6 Compliant UL Listed to UL498 File No. E2186
Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Pallet Quantity	9000

## Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
- [Warranty - Industrial & Commercial Products](#)

