

Straight Blade Devices, Female Connector Body, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 15A 125V, 5-15R, Extra Large

By Hubbell Wiring Device-Kellems
Catalog # [HBL5269EBK](#)

Straight Blade Devices, Female Connector Body, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2- Pole 3-Wire Grounding, 15A 125V, 5-15R, Black, Single Pack, Extra Large

Features

- Individual wiring terminals completely enclosed
- Powerful, offsetting cord grips clamp on individual conductors
- Fast lead assembly screws
- Beveled housing prevents snagging

Application

Industrial/Commercial Grade

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 HB or better, Environmental - IP Suitability - IP20, Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact), Mechanical - Terminal Accommodation - #18-10 AWG. Standed copper wire only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Specifications

Standards - RoHS Compliance Status	CM
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R
Industry Standard(s)	• CSA Certified to C22.2 No. 42 File 280 • NEMA® WD-6 Compliant • UL Listed to UL498 File E1706

Conductor

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG
Number Of Poles	2-Pole
Conductor Range	#18 AWG to #10 AWG

Current

Amperage Rating	15 A
-----------------	------



Voltage Rating Description	125 V
Dielectric Strength	Withstands 2,000V minimum
Current Rating	15 A
Voltage Rating	125 VAC
Connectivity	Screw Terminals
Phase	Single Phase
Current / Amperage Rating	15 A

Dimensions

Display Size	Standard
Weight	0.2 lb.

General

Color	Black
Style	Standard
Cord Range	0.250"-0.655" (6.4-16.6)
Series	Insulgrip®
Specifications	• Assembly Screws - Nickel plated steel • Contact Holder - Nylon • Contacts - .040 in. (1.0) Brass • Housing/Cord Clamp - Nylon • Terminal Clamp - Nickel plated steel • Terminal Retainer - Clear Polycarbonate • Terminal Screws - #8-32 Brass , multiple drive
UPC	783585366128
Type	Connector Body
Material - Mounting Hardware	Cord Mounted
Insulation	Insulated Body
Item Type	Insulgrip Plug
Material	Polycarbonate

Logistics

Pallet Quantity	3600
Carton Quantity	10

Operational

Temperature Rating	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Horsepower - Maximum	0.50

Product Assets

- Catalog [English]
- Catalog Page [English]
- Installation Manual [French]



A Hubbell brand