

GFP100C15WM

By Hubbell Wiring Device-Kellems
Catalog # [GFP100C15WM](#)

Power Protection Products, GFCI Linecords, Commercial, Manual Set, 15A, 120V AC, 5-15R, 100' Cord Length, 4-6 mA Trip Level, Black and Yellow



Application

Line Cord with Male/Female Ends

General

Catalog Number	GFP100C15WM
Color	Black
Construction	Fabricated
EU RoHS Indicator	No
Item Type	Straight Blade
Material - Insulation	Elastomer
Material - Jacket	PVC
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none">Covers - PVCLoad Cord - PVC
Style	Manual Set
Temperature Rating	-35 Degrees C to 66 Degrees C (-30 Degrees F to 150 Degrees F)
Type	Line Cord
UPC	783585829333

Dimensions

Outside Diameter	0.245
------------------	-------

Weight	16.85 lb
--------	----------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC

Conductor Related

Conductor Size	#14 AWG
Conductor Type	Copper
Number of Conductors	3
Strands	Multi

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - GFP100C15WM](#)