

Straight Blade Devices,
Receptacles, Duplex, Corrosion
resistant, 2-Pole 3-Wire Grounding,
15A 125V, 5-15R, Ivory, Single Pack,
Chem-Marine

By Hubbell Wiring Device-Kellems
Catalog # [HBL52CM62I](#)



Straight Blade Devices, Receptacles, Duplex, Marine Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Ivory, Single Pack, Chem-Marine.

Features

- Back wired ground terminal allows faster, easier installation
- One-piece brass integral ground strap
- Finder Groove Face
- Deep body design with circuit ID face
- Corrosion resistant

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - Top: UL 94V-2, Base: UL 94V-0
- Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	HBL52CM62I
EU RoHS Indicator	Yes
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	HBL Extra Heavy Duty
Specifications	<ul style="list-style-type: none">• Automatic Self-grounding Clip - Stainless steel• Base - PBT• By-Pass Power Contacts - .036". (.9) Nickel plated brass

Style	Clamping Plate - Nickel plated brass
UPC	Face - Nylon
	Ground Contacts - .031 in. (.8) Brass
	Mounting Screws - Stainless steel
	Mounting Strap - .050 in. (1.3) Nickel plated brass
	Terminal Screws - Plated brass
	Corrosion Resistant
	Finder Groove Face
	783585411026

Dimensions

Dimensions	3.28 in x 1.65 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	3.28 in
Weight	0.25 lb
Width	1.65 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA 22.2, No. 42 File 285• Fed. Spec. WC596• NEMA® WD-6 Compliant• UL Listed to UL498 File No. E2186
Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- Catalog Page - WDK AA-43 Catalog Page
- Catalog Page - WDK AA-37 Catalog Page
- Catalog Page - WDK A-10 Catalog Page
- Catalogs - WDK Catalog Full 2024
- Engineering Drawing - HBL52CM62I AutoCAD Drawing
- Installation Manuals - WIRING_PD1555_INSTALLINST
- Literature - Hubbell Marine Full Line Catalog
- Sales Drawings - WDK_HBL52CM62I_DRAWINGS_PDF
- Specifications - Wiring HBL52CM62I Specification Sheet
- Specifications - HBL52CM62I Specification Sheet
- Specifications - HBL52CM62I Specification Sheet French
- Warranty - Industrial & Commercial Products
- Video - Marine Electrical Products
- Video - Marine Electrical Products



A Hubbell brand