



Wiring Device-Kellems

# Kellems Wire Management, Liquidtight System, Straight Male Liquid Tight Connector, 3/4", Steel, Insulated

By Hubbell Wiring Device-Kellems  
Catalog # [H0751](#)



Kellems Wire Management, Liquidtight System, Straight Male Liquid Tight Connector, 3/4", Steel, Insulated

## Features

- Hexagonal nut compresses gland-ring onto conduit
- Nylon gasket provides liquidtight seal at hub
- Non-integral steel ferrule seals conduit

## Application

For use with Liquidtight Metal conduit and PolyTuff I Non-Metallic conduit

## General

Material	Steel, Zinc Plated
Performance	<ul style="list-style-type: none"> <li>• Environmental - Operating Temperature - -60°F to +1000°F (-51°C to +538°C)</li> <li>• Environmental - Hazardous Locations - NEC Reference -Class I, Div. 2 - 501-10(A)(3)B, Class II, Div. 1 - 502-10(A)(2), Class II, Div. 2 - 502-10(A)(3), Class III, Div. 1 - 503-10(A)(2), Class III, Div. 2 - 503-10(B)</li> </ul>
Style	Straight
Type	<ul style="list-style-type: none"> <li>• Metallic Liquidtight Fittings</li> <li>• Metallic Liquidtight Fittings</li> </ul>
UPC	783585035130

## Dimensions

Dimension - L Length Overall mm	1.562 in
Dimension - Thread Size	3/4"-14 NPT
Dimension - Width mm	1.453 in
Trade Size	3/4

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified</li> <li>• UL 514B</li> </ul>
----------------------	--

## Logistics

Carton Quantity	25
-----------------	----

## Product Assets

- [Catalogs - WDK Catalog Full 2023](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.