



# Kellems Wire Management, Liquidtight System, Straight Male Liquid Tight Connector, 1 1/2", Steel, Insulated

By Hubbell Wiring Device-Kellems  
Catalog # [H1501](#)



Kellems Wire Management, Liquidtight System, Straight Male  
Liquid Tight Connector, 1 1/2", Steel, Insulated

## Features

- Hexagonal nut compresses gland-ring onto conduit
- Nylon gasket provides liquidtight seal at hub
- Non-integral steel ferrule seals conduit

## Application

For use with Liquidtight Metal conduit and PolyTuff I Non-Metallic conduit

## General

Material	Iron, Zinc Plated
Performance	<ul style="list-style-type: none"><li>• Environmental - Operating Temperature - -60°F to +1000°F (-51°C to +538°C)</li><li>• Environmental - Hazardous Locations - NEC Reference -Class I, Div. 2 - 501-10(A)(3)B, Class II, Div. 1 - 502-10(A)(2), Class II, Div. 2 - 502-10(A)(3), Class III, Div. 1 - 503-10(A)(2), Class III, Div. 2 - 503-10(B)</li></ul>
Style	Straight
Type	<ul style="list-style-type: none"><li>• Metallic Liquidtight Fittings</li><li>• Metallic Liquidtight Fittings</li></ul>
UPC	783585035161

## Dimensions

Dimension - L Length Overall mm	2.219 in
Dimension - Thread Size	1-1/2"-11-1/2 NPT
Dimension - Width mm	2.500 in
Trade Size	1 1/2

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Certified</li><li>• UL 514B</li></ul>
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	2
-----------------	---

## Product Assets

[Catalogs - WDK Catalog Full 2023](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-H1501-SPEC-EN | REV 1/2024