

Extra Heavy Duty Industrial Grade,  
Locking Toggle Switches, General  
Purpose AC, Single Pole, 15A  
120/277V AC, Back and Side Wired  
Key Guide

By Hubbell Wiring Device-Kellems  
Catalog # [HBL1201L](#)



Switches and Lighting Controls,Extra Heavy Duty Industrial  
Grade, Locking Toggle Switches, General Purpose AC, Single  
Pole, 15A 120/277V AC, Back and Side Wired, Black Key Guide

Application

- Back and Side Wired

Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 15A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only

General

|                       |   |
|-----------------------|---|
| Catalog Number        | HBL1201L  |
| Color                 | Black   |
| EU RoHS Indicator     | No  |
| Number Of Poles       | Single Pole   |
| Operating Temperature | Maximum continuous 75°C and minimum -40°C without Impact  |
| Series                | Extra Heavy Duty  |
| Specifications        | <ul style="list-style-type: none"><li>• Base Material - Thermoset, Blue</li><li>• Contacts - Silver Alloy</li><li>• Ground Screw - Brass (Green)</li><li>• Key Guide - Metallic, Black</li><li>• Terminal Screws - Brass</li><li>• Top Material - Thermoset</li></ul> |
| Style                 | Single Pole   |
| Type                  | Locking   |

UPC783585430089

Dimensions

|            |                             |
|------------|-----------------------------|
| Dimensions | 4.06 in x 1.31 in x 1.13 in |
| Height     | 1.13 in                     |
| Length     | 4.06 in                     |
| Weight     | 0.2 lb                      |
| Width      | 1.31 in                     |

Electrical Ratings

|                            |  |
|----------------------------|--|
| Amperage Rating            | 15 A                                     |
| Connectivity               | Back and Side Wired                      |
| Current / Amperage Rating  | 15 A                                     |
| Current Rating             | 15 A                                     |
| Dielectric Strength        | Withstands 1500V AC minimum for 1 minute |
| Temperature Rise - Max.    | 30°C maximum at rated current            |
| Voltage Rating             | 120-277 VAC                              |
| Voltage Rating Description | 120-277 VAC                              |

Conductor Related

Wire Size#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)UL Listed

Logistics

|                 |      |
|-----------------|------|
| Carton Quantity | 10   |
| Pallet Quantity | 4500 |

Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL1201L](#)  
[Warranty - Industrial & Commercial Products](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL1201L-SPEC-EN | REV 10/2024