

Industrial Grade, Barrel Key Locking Switch, General Purpose AC, Double Pole, 20A 120/277V AC, Back and Side Wired, Chrome

By Hubbell Wiring Device-Kellems
Catalog # [HBL1222RKL](#)



Switches and Lighting Controls, Industrial Grade, Barrel Key Locking Switch, General Purpose AC, Double Pole, 20A 120/277V AC, Back and Side Wired, Chrome

Application

Back and Side Wired

Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 20A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only

General

Catalog Number	HBL1222RKL
Color	Chrome
EU RoHS Indicator	No
Number Of Poles	Double Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none">• Base Material - Thermoset, Red• Contacts - Silver Alloy• Ground Screw - Brass (Green)• Key Guide - Chrome• Terminal Screws - Brass• Top Material - Thermoset
Style	Double Pole
Type	Locking

UPC 783585431734

Dimensions

Dimensions	4.06 in x 1.25 in x 2.02 in
Height	2.02 in
Length	4.06 in
Weight	0.2 lb
Width	1.25 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

Conductor Related

Wire Size #14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s) UL Listed

Logistics

Carton Quantity 10

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Healthcare Product Solutions](#)
[Specifications - HBL1222RKL](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL1222RKL-SPEC-EN | REV 10/2024