

Locking Devices, Twist-Lock®,
Marine Grade, Receptacle, 50A
125V, 2-Pole 3-Wire Grounding,
Non-NEMA, Screw Terminal,
Galvanized

By Hubbell Wiring Device-Kellems
Catalog # [HBL63CM70](#)

Locking Devices, Twist-Lock®, Marine Grade, Receptacle, 50A
125V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal,
Galvanized

Features

- Marine Grade
- Receptacle
- 50A 125V

Application

Marine Wiring Devices

Performance

Environmental - Moisture Resistance - IP20 Suitability

General

Catalog Number	HBL63CM70
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none">• Base Material - Thermoset base• Blade Type - Locking• Product Type - Receptacles• Receptacle Style - Single• Receptacle Type - Corrosion Resistant
UPC	783585808758

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings



Amperage Rating	50 A
Connectivity	Screw Terminals
Current / Amperage Rating	50 A
Current Rating	50 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	6250

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#6 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	Non-NEMA

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog Page - WDK AA-15 Catalog Page](#)
- [Catalog Page - WDK AA-5 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - HBL63CM70 AutoCAD Drawing](#)
- [Literature - Hubbell Marine Full Line Catalog](#)
- [Sales Drawings - WDK_HBL63CM70_DRAWING_PDF](#)
- [Specifications - WIRING_HBL63CM70_spec](#)
- [Specifications - HBL63CM70 Specification Sheet](#)
- [Specifications - HBL63CM70 Specification Sheet French](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Marine Electrical Products](#)
- [Video - Marine Electrical Products](#)