

HUBBELL
Wiring Device-Kellems

**Extra Heavy Duty Industrial Grade,
Toggle Switches, General Purpose
AC, Three Way, 20A 120/277V AC,
Back and Side Wired, Brown Toggle**

By Hubbell Wiring Device-Kellems
Catalog # [HBL1223](#)

Switches and Lighting Controls, Extra Heavy Duty Industrial
Grade, Toggle Switches, General Purpose AC, Three Way, 20A
120/277V AC, Back and Side Wired, Brown Toggle



General

Action	SPDT
Application	Back and Side Wired
Catalog Number	HBL1223
Color	Brown
EU RoHS Indicator	No
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
	Electrical - Max. Continuous Current - 20A
	Electrical - Max. Working Voltage - 277V AC
	Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
	Electrical - Temperature Rise - 30°C maximum at rated current
	Environmental - Flammability - UL 94V-2
	Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
	Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only
Series	Extra Heavy Duty
Style	Three Way
Type	Toggle
	Toggle
UPC	783585431765

Dimensions

Dimensions	4.06 in x 1.31 in x 1.87 in
Height	1.87 in
Length	4.06 in
Weight	0.2 lb
Width	1.31 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
Pallet Quantity	4050

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL1223-SPEC-EN | REV 6/2024