



Wiring Device-Kellems

Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 6) Receptacles, Metallic Body, 1050 Joules, 6' Cord

By Hubbell Wiring Device-Kellems
Catalog Number [HBL6MPS1050](#)



Surge Protective Devices, SPIKESHIELD TVSS Plug Strips, 6) Receptacles, Metallic Body, 1050 Joules, 6' Cord.

Features

- Yellow color for high visibility and metal housing
- 350 joules, 6 foot cord, wire management

Application

Standard Devices

General

Color	Office White
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	LED Indicator
Item Type	Surge Protection Plug Strips
Material	Steel
Material - Mounting Hardware	Portable
Number Of Outlets	6
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade 5-15R
Performance	<ul style="list-style-type: none"> • Electrical - Max Surge Current - 19.5kA • Electrical - Max. Operating Voltage - 130 • Electrical - Operating Frequency - 50/60Hz • Environmental - Operating Temperature - -40°F to 160°F (-40°C to 70°C)
Response Time	5
Series	Economy Surge Strips
Type	Metallic
UPC	783585120676

Dimensions

Display Size 1050 Joules

Electrical Ratings

Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Frequency Rating	60 Hz
Phase	Single Phase

Conductor Related

Cord Length 6 ft

Logistics

Carton Quantity 20

Product Assets

[Catalog Page - Wiring N-9 Catalog page](#)
[Installation Manuals - WIRING_PD2380_INSTALLINST Literature - SpikeShield® Power Quality Surge Protective Devices](#)
[Warranty - Surge Plug Strips](#)



A proud member of the Hubbell Family.