

HUBBELL
Wiring Device-Kellems

**Locking Devices, Twist-Lock®, Industrial,
Combination Face Duplex Receptacle, 15A
125V/10A 250V, 15A 125 V, 2-Pole 3-Wire
Grounding**

By Hubbell Wiring Device-Kellems
Catalog # [HBL7371](#)

Locking Devices, Twist-Lock®, Industrial, Combination Face
Duplex Receptacle, 15A 125V/10A 250V, 15A 125 V, 2-Pole 3-Wire
Grounding, 5-15R and Non NEMA, Screw Terminal, Brown, 2)
Feeds 1) Return



Features

- Industrial
- Combination Face Duplex Receptacle
- 15A 125V/10A 250V

Application

Heavy Duty

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 V-2 or better, Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact), Mechanical - Product Identification - Ratings are a permanent part of the device, Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only, Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes
Nema Rating	5-15R
Industry Standard(s)	• Certified to CSA, C22.2, No. 42 File 285 • UL Listed to UL498 File E2186

Conductor

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	15 A
Voltage Rating Description	• 125 V • 250 V

Dielectric Strength	Withstands 2,000V minimum
Current Rating	15 A
Voltage Rating	125/250 V
Wattage	1875 W
Connectivity	Screw Terminals
Phase	Single Phase
Current / Amperage Rating	15/10 A,15 A

Dimensions

Length	3.28 in
Display Size	Standard Sized Product
Weight	0.25 lb.
Height	0.88 in
Width	1.5 in
Dimensions	3.28 in x 1.5 in x 0.88 in

General

Color	Brown
Specifications	• Base - RTP • Face - Reinforced thermoplastic polyester • Power Contacts - .032" (.81) Brass
UPC	783585237152
Material - Mounting Hardware	Screw Mounting
Item Type	Combination Duplex Receptacles

Logistics

Carton Quantity	10
-----------------	----

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Horsepower - Maximum	0.5

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)



A Hubbell brand