

Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 30A 600V AC, Back and Side Wired, In NEMA 1 Non Metallic Enclosure

By Hubbell Wiring Device-Kellems
Catalog # [HBL1392D](#)



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 30A 600V AC, Back and Side Wired, Black, In NEMA 1 Non Metallic Enclosure

Application

Standard Toggle

Performance

- Electrical - Dielectric Voltage - Min. 2,200V AC minimum for 1 minute
- Electrical - Electrical Life - Min. 6,000 Cycles at rated switch load
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94HB/VO
- Environmental - Operating Temperature - Max. 75°C, Min. -40°C continuous w/o impact
- Mechanical - Mechanical Life - Min. 10,000 minimum cycles
- Mechanical - Switch Rating - 25 inch pounds
- Mechanical - Terminal Accommodations - #10 AWG Max
- Mechanical - Terminal Torque - 20 inch pounds
- Mechanical - Wire Type - Solid and stranded copper wire only

General

Catalog Number	HBL1392D
Construction	Fabricated
EU RoHS Indicator	No
Enclosure Type	NEMA 1
Environmental Conditions	Indoor and Outdoor
Horsepower - Maximum	15
Load Capacity	Inductive
Material - Mounting Hardware	Screw Mounting
Operating Cycles	10,000 Cycles Minimum
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Non-Fused
Specifications	Enclosure Material - Thermoplastic
Style	Standard Duty

Type Disconnect Switches
UPC 783585202631

Dimensions

Dimensions	4.52 in x 3.97 in x 3.43 in
Display Size	Standard Sized Product
Height	3.43 in
Length	4.52 in
Weight	1.5 lb
Width	3.97 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	2,200V AC minimum for 1 minute
Phase	Single Phase
Wattage	18000 W

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">CSA-C22.2 No.14 Industrial Control File LR-46186UL 508, Industrial Control File #E70402
----------------------	--

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL1392D](#)