



Wiring Device-Kellems

Locking Devices, Midget Twist-Lock®, Industrial, Flanged Receptacle, 15A 125V AC, 2-Pole 2-Wire Non Grounding, NEMA ML-1R, Stainless Steel Flange.

By Hubbell Wiring Device-Kellems
Catalog # [HBL7468](#)



Twist-Lock® Non-Grounding Midget Flanged Receptacle 15A, 125V, 2-Pole 2-Wire, NEMA ML-1R, Stainless Steel.

Features

- Stainless Steel mounting flange
- High heat resistant phenolic base
- Stainless steel mounting flange

Application

Heavy Duty Industrial

General

Color	<ul style="list-style-type: none"> • Stainless Steel • Acier inoxydable
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Midget Twist-Lock® Flanged Receptacle
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17 • Environmental - Moisture Resistance - IP20 Suitability • Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact) • Mechanical - Terminal Accommodation - #18 AWG - #14 AWG solid or

Dimensions

Dimensions	1.63 in x 1.63 in x 0.78 in
Display Size	Midget Locking
Height	0.78 in
Length	1.63 in
Weight	0.05 lb
Width	1.63 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	2-Wire
Wire Size	#18 AWG to #14 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Listed to UL 498
Nema Rating	ML-1R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK B-7 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Literature - Insulgrip® Straight Blade and Twist-Lock® Devices](#)
- [Sales Drawings - WDK_HBL7468_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Twist-Lock Devices](#)

Related Products

stranded copper wire only.

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

HBL7465V - Locking Devices, Midget Twist-Lock®, Valise®, Male Plug, 15A 125V, 2-Pole 2-Wire Non Grounding, NEMA ML-1P, Screw Terminal, Black.

Temperature Rating

Maximum continu : 75° C ;
Minimum continu : -40° C sans impact, -25° avec impact.

Type

- Flanged Receptacle
- Flanged Receptacle

UPC

783585237336



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL7468-SPEC-EN | REV 1/2024