

Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 30A 600V AC, Back and Side Wired, In NEMA 1 Non Metallic Enclosure

By Hubbell Wiring Device-Kellems
Catalog # [HBL1392D](#)



Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 30A 600V AC, Back and Side Wired, Black, In NEMA 1 Non Metallic Enclosure

Application

Standard Toggle

Performance

- Electrical - Dielectric Voltage - Min. 2,200V AC minimum for 1 minute
- Electrical - Electrical Life - Min. 6,000 Cycles at rated switch load
- Electrical - Max. Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94HB/VO
- Environmental - Operating Temperature - Max. 75°C, Min. -40°C continuous w/o impact
- Mechanical - Mechanical Life - Min. 10,000 minimum cycles
- Mechanical - Switch Rating - 25 inch pounds
- Mechanical - Terminal Accommodations - #10 AWG Max
- Mechanical - Terminal Torque - 20 inch pounds
- Mechanical - Wire Type - Solid and stranded copper wire only

General

| | |
|------------------------------|--|
| Catalog Number | HBL1392D |
| Construction | Fabricated |
| EU RoHS Indicator | No |
| Enclosure Type | NEMA 1 |
| Environmental Conditions | Indoor and Outdoor |
| Horsepower - Maximum | 15 |
| Load Capacity | Inductive |
| Material - Mounting Hardware | Screw Mounting |
| Operating Cycles | 10,000 Cycles Minimum |
| Operating Temperature | Maximum continuous 75°C and minimum -40°C without Impact |
| Series | Non-Fused |
| Specifications | Enclosure Material - Thermoplastic |
| Style | Standard Duty |

Type
UPC

Disconnect Switches
783585202631

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 4.52 in x 3.97 in x 3.43 in |
| Display Size | Standard Sized Product |
| Height | 3.43 in |
| Length | 4.52 in |
| Weight | 1.5 lb |
| Width | 3.97 in |

Electrical Ratings

| | |
|---------------------------|--------------------------------|
| Amperage Rating | 30 A |
| Connectivity | Pressure Terminal Screws |
| Current / Amperage Rating | 30 A |
| Current Rating | 30 A |
| Dielectric Strength | 2,200V AC minimum for 1 minute |
| Phase | Single Phase |
| Wattage | 18000 W |

Certifications And Compliance

| | |
|----------------------|--|
| Industry Standard(s) | <ul style="list-style-type: none">CSA-C22.2 No.14 Industrial Control File LR-46186UL 508, Industrial Control File #E70402 |
|----------------------|--|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL1392D](#)