



# Locking Devices, Midget Twist-Lock®, Industrial, Female Valise® Connector, 15A 125/250V AC, 3-Pole 3-Wire Non Grounding, NEMA ML-3R

By Hubbell Wiring Device-Kellems  
Catalog # [HBL7484V](#)



Twist-Lock® Valise® Non-Grounding Midget Female Connector  
15A, 125/250V, 3-Pole 3-Wire, NEMA ML-3R.

## Features

- Fully insulated, abuse resistant nylon housing
- Insulation displacement terminals reduce wiring time

## Application

Heavy Duty Industrial

## General

Color	<ul style="list-style-type: none"> <li>• Black</li> <li>• Noir</li> </ul>
Cord Range	0.300"-0.430"(7.6-10.9)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Insulation	Insulated Body
Item Type	15A Midget Twist-Lock® Valise® Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17</li> <li>• Environmental - Moisture Resistance - IP20 Suitability</li> <li>• Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)</li> <li>• Mechanical - Terminal Accomodation - #18 AWG - #14 AWG stranded copper wires only</li> </ul>

## Dimensions

Dimensions	1.19 in x 1.19 in x 1.98 in
Display Size	Midget Locking
Height	1.98 in
Length	1.19 in
Weight	0.10 lb
Width	1.19 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Insulation Displacement
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125/250 V
Voltage Rating Description	125/250 V

## Conductor Related

Cable Range	0.300 - 0.430 in
Conductor Range	#14 AWG to #12 AWG
Number Of Wires	3-Wire
Wire Size	#18 AWG to #14 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Listed to UL 498</li> </ul>
Nema Rating	ML-3R
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - WDK B-7 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Installation Manuals - WIRING\\_PD2441\\_INSTALLINST](#)  
[Literature - Insulgrip® Straight Blade and Twist-Lock® Devices](#)  
[Sales Drawings - WDK\\_HBL7484V\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)  
[Video - Twist Lock Devices](#)

wire only.

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

Temperature Rating

Maximum continu : 75° C ;  
Minimum continu : -40° C sans impact, -25° avec impact.

Type

- Connector Body
- Connector Body

UPC

783585237398

## Related Products

[HBL7440V - Locking Devices, Midget Twist-Lock®, Accessories, Weatherproof Boot 15A For 3-Wire, Black](#)

[HBL7486N - Locking Devices, Midget Twist-Lock®, Industrial, Flanged Inlet, 15A 125/250V AC, 3-Pole 3-Wire Non Grounding, NEMA ML-3P, Screw Terminal Nylon Flange.](#)

[HBL7485 - Locking Devices, Midget Twist-Lock®, Industrial, Male Plug, 15A 125/250V AC, 3-Pole 3-Wire Non Grounding, NEMA ML-3P, Screw Terminal, Black.](#)

[HBL7486 - Locking Devices, Midget Twist-Lock®, Industrial, Flanged Inlet, 15A 125/250V AC, 3-Pole 3-Wire Non Grounding, NEMA ML-3P, Stainless Steel Flange.](#)

[HBL7495V - Locking Devices, Midget Twist-Lock®, Industrial, Weatherproof Boot, For 3-Wire, Black](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL7484V-SPEC-EN | REV 1/2024