

Straight Blade Devices, Thermoplastic Elastomer Water Tight, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 20A 125V, 5-20P.



By Hubbell Wiring Device-Kellems
Catalog # [HBL14W33A](#)

Straight Blade Devices, Thermoplastic Elastomer Water Tight,
Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding,
20A 125V, 5-20P, Yellow, Single Pack.

Performance

- Electrical:Current Interrupting Rated for current interruption per UL498
- Dielectric Voltage: 2500V AC
- Max Working Voltage As marked
- Temperature Rise: 30°C max per UL498 at rated current
- Mechanical:Cord Accomodation: 0.375"-0.625" (9.5-15.9)
- Environmental:Moisture Resistance UL Listed 4, 4X, 12, 6, 6P
- Operating temperatures -40°C (without impact) to +60°C continuous
- UV resistance All exposed materials are UV stabilized

General

Catalog Number	HBL14W33A
Color	Yellow
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	2-Pole
Operating Temperature	-40°C (without impact) to +60°C continuous
Series	Watertight Devices
Temperature Rating	-40°C (without impact) to +60°C continuous
Type	Plugs
UPC	783585131184

Dimensions

Weight	0.2 lb
--------	--------

Electrical Ratings

Amperage Rating	20 A
-----------------	------

Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• IP69K rating• Listed to UL498• Certified to CSA C22.2 No. 42• Meets NEMA WD-1, WD-6 And ANSI Standards• UL Listed, CSA Certified to Type 4, 4X, 12, 6, 6P
Nema Rating	5-20P
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	25
Pallet Quantity	2025

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Watertight Wiring Devices Flyer](#)
[Specifications - HBL14W33A](#)
[Warranty - Industrial & Commercial Products](#)