



# Locking Devices, Twist-Lock®, Industrial, Flanged Receptacle, 10A 250V/15A 125V, 3-Pole 3-Wire Non Grounding, Non- NEMA, Screw Terminal, Steel

By Hubbell Wiring Device-Kellems  
Catalog # [HBL7557](#)



Locking Devices, Twist-Lock®, Industrial, Stainless Steel Flanged Receptacle, 10A 250V/15A 125V, 3-Pole 3-Wire Non Grounding, Non- NEMA, Screw Terminal, Brown/Stainless.

## Features

- Heat resistant thermoset construction
- Stainless steel casing
- #8-32 terminal screws
- Mounting screws included

## Application

Heavy Duty Industrial

## General

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	10A/15A Non-Grounding Stainless Steel Flanged Receptacle
Material	Stainless Steel
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17</li> <li>• Environmental - Moisture Resistance - IP20 Suitability</li> <li>• Environmental - Operating Temperatures - Maximum Continuous 75°C Minimum -40°C (w/o impact)</li> <li>• Mechanical - Terminal Accommodation - #18 AWG -#10 AWG solid or stranded copper wire only.</li> </ul>

## Dimensions

Dimensions	2.31 in x 1.75 in x 1.32 in
Display Size	Standard Sized Product
Height	1.32 in
Length	2.31 in
Weight	0.15 lb
Width	1.75 in

## Electrical Ratings

Amperage Rating	10/15 A
Connectivity	Screw Terminals
Current / Amperage Rating	10/15 A
Current Rating	10 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250/125 V
Voltage Rating Description	250/125 V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed. Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
----------------------	--

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - WDK B-43 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Sales Drawings - WDK\\_HBL7557\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Insulgrip Twist-Lock and Straight Blade Devices](#)

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

Type

- Receptacle
- Receptacle

UPC

783585237664



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_CA-HBL7557-SPEC-EN | REV 1/2024