

# Straight Blade Devices, Male Plug, Elasto-Grip Water Tight, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P



By Hubbell Wiring Device-Kellems  
Catalog # [HBL14W47](#)

Straight Blade Devices, Male Plug, Elasto-Grip Water Tight, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Yellow, Single Pack.

## Application

- Industrial/Commercial Grade

## Performance

- Electrical:Current Interrupting Certified for current interrupting at full rated current
- Dielectric Voltage: Withstands 2,000V minimum
- Mechanical:Product Identification: Ratings are a permanent part of the device
- Terminal Accommodation:#18-#12 AWG. Stranded copper wire only.
- Terminal Identification: Terminals identified in accordance with UL 498 and CSA
- Environmental:Flammability: UL 94 V-2
- IP Suitability: IP55
- Operating Temperatures: Maximum continuous 75°C
- minimum -40°C (w/o impact)

## General

Catalog Number	HBL14W47
Color	Jaune
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.5
Item Type	Insulgrip Plug
Material	Polycarbonate
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Elastogrip
Specifications	<ul style="list-style-type: none"> <li>Assembly Screws - Plated steel</li> <li>Blade Holder - Nylon</li> <li>Blades - .060" (1.5) Brass</li> <li>Housing - PVC</li> <li>Terminal Clamp - Nickel plated steel</li> <li>Terminal Retainer - Clear Polycarbonate</li> </ul>

Style	Standard
Type	Plug
UPC	783585013008
	<ul style="list-style-type: none"> <li>Terminal Screws - #8-32 Brass , multiple drive</li> </ul>

## Dimensions

Dimensions	2.65 in x 1.55 in x 2.65 in
Height	2.65 in
Length	2.65 in
Weight	0.2 lb
Width	1.55 in

## Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#18 AWG to #12 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>CSA Certified to C22.2 No. 42 File 280</li> <li>NEMA® WD-6 Compliant</li> <li>UL Listed to UL498 File E1706</li> </ul>
Nema Rating	5-15P

## Logistics

Carton Quantity	10
Pallet Quantity	4050



A Hubbell brand