




Wiring Device-Kellems

Locking Devices, Twist-Lock®, Industrial, Male Plug, 10A 250V/15A 125V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal, Black and White



By Hubbell Wiring Device-Kellems
Catalog # [HBL7567C](#)

Insulgrip® Straight Blade Non-Grounding Male Plug 10A 250V, 15A 125V, 3-Pole 3-Wire, Non-NEMA/White Nylon.

Features

- Individually molded face for each blade configuration keeps debris out of plug interior
- Ribbed nylon housing is impact and chemical resistant
- Roomy wiring chamber provides ample space for wiring

Application

Extra Heavy Duty Industrial

General

Color	Black, White
Cord Range	0.230"-0.720"(5.8-18.3)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	10A/15A Insulgrip® Plug
Listings	<ul style="list-style-type: none"> • Fed.Spec. W-C-596 • CSA C22.2 No.42
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical-Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Mechanical - Terminal Accommodation - #18 - #10 AWG stranded copper wire only • Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 • Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17 • Environmental - Moisture

Dimensions

Dimensions	1.53 in x 1.53 in x 1.97 in
Display Size	Standard Sized
Height	1.97 in
Length	1.53 in
Weight	0.15 lb
Width	1.53 in

Electrical Ratings

Amperage Rating	10 A
Connectivity	Screw Terminals
Current / Amperage Rating	10 A
Current Rating	10 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250/125 V
Voltage Rating Description	250/125 V

Conductor Related

Cord Type	All Listed Portables
Number Of Wires	3-Wire Non-Grounding
Wire Size	#18 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed.Spec.W-C-596
Nema Rating	Non-NEMA
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK B-43 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBL7567C AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1265_INSTALLINST](#)
- [Sales Drawings - WDK_HBL7567C_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Insulgrip Twist Lock and Straight Blade Devices](#)

Resistance - IP20
Suitability

- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum -40°C (w/o impact)

UPC

783585178752

Related Products

[HBL7565C - Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 10A 250V/15A 125V, 3-Pole 3-Wire Non Grounding, Non-NEMA, Screw Terminal and White](#)

[HBL7582 - Locking Devices, Twist-Lock®, Industrial, Single Flush Receptacle, 10A 250V, 15A 125V, 3-Pole 3-Wire Non-Grounding, Non-NEMA, Screw Terminal Phenolic.](#)

[HBL7580 - Locking Devices, Twist-Lock®, Industrial, Duplex Receptacle, 10A 250/15A 125V, 2-Pole 3-Wire Grounding, Non-NEMA, Screw Terminal, Black](#)

[HBL7557 - Locking Devices, Twist-Lock®, Industrial, Flanged Receptacle, 10A 250V/15A 125V, 3-Pole 3-Wire Non Grounding, Non- NEMA, Screw Terminal, Steel](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL7567C-SPEC-EN | REV 1/2024