

**HUBBELL**  
Wiring Device-Kellems

## **Industrial Grade, Locking Switches, General Purpose AC, Momentary Single Pole Double Throw Center Off, 15A 120/277V AC Black Key Guide**

By Hubbell Wiring Device-Kellems  
Catalog # [HBL1556L](#)

Switches and Lighting Controls, Industrial Grade, Locking  
Switches, General Purpose AC, Momentary Single Pole Double  
Throw Center Off , 15A 120/277V AC, Terminal Screws Black Key  
Guide



## Application

- Back and Side Wired

## Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 15A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. Solid and stranded copper wire only

## General

Action	SPDT
Catalog Number	HBL1556L
Color	Black
Contact Configuration	Momentary
EU RoHS Indicator	No
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Extra Heavy Duty
Specifications	<ul style="list-style-type: none"><li>• Base Material - Thermoset, Blue</li><li>• Contacts - Silver Alloy</li><li>• Ground Screw - Brass (Green)</li><li>• Key Guide - Metallic, Black</li><li>• Terminal Screws - Brass</li><li>• Top Material - Thermoset</li></ul>

Style  
Type  
UPC

Single Pole Double Throw  
Locking  
783585432809

## Dimensions

Dimensions	4.06 in x 1.31 in x 1.89 in
Height	1.89 in
Length	4.06 in
Weight	0.2 lb
Width	1.31 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

## Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

## Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - HBL1556L](#)  
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-HBL1556L-SPEC-EN | REV 10/2024