

Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 50A 250V/600V AC, Non-NEMA, Screw Terminal, Zinc plated steel casing, thermoset interior

By Hubbell Wiring Device-Kellems
Catalog # [HBL7958](#)

Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 50A 250V/600V AC, 3-Pole 4-Wire Grounding, Non-NEMA, Screw Terminal, Zinc plated steel casing, thermoset interior, Metallic

Features

- Metallic flanged casing provides maximum strength and protection
- Thermoset interior provides superior heat resistance

Application

Extra Heavy Duty Industrial

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current, Electrical - Dielectric Voltage - Withstands 2,000V minimum, Environmental - Flammability - UL 94 V0, Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact), Mechanical - Terminal Accommodation - #10 AWG - #6 AWG solid or stranded copper wire only

Specifications


Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	No
Industry Standard(s)	• Certified to CSA C22.2 No.42 • Listed to UL 498

Conductor

Number Of Wires	4-Wire
Wire Size	#8 AWG to #4 AWG
Number Of Poles	3-Pole

Current

Amperage Rating	50 A
Voltage Rating Description	250 VDC/600 VAC
Dielectric Strength	Withstands 2,000V minimum
Current Rating	50 A



Voltage Rating	250 VDC/600 VAC
Connectivity	Pressure Terminal Screws
Phase	Three Phase
Current / Amperage Rating	50 A

Dimensions

Length	2.14 in
Display Size	Standard Sized Product
Weight	0.85 lb.
Height	2.62 in
Width	3.50 in
Dimensions	2.14 in x 3.50 in x 2.62 in

General

Color	Metallic
Specifications	• Blades - Brass • Casing - Steel, zinc plated • Terminal Retainer - Phenolic • Terminal Screws - Steel
UPC	783585237589
Type	Flanged Inlet
Material - Mounting Hardware	Screw Mounting
Item Type	50A Flanged Inlet
Material	Steel, Zinc Plated

Logistics

Carton Quantity	10
-----------------	----

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
-----------------------	--

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[French\]](#)