

Single Pole Products, Female Receptacle, Double Set Screw Termination, 150 Amp Series, White

By Hubbell Wiring Device-Kellems
Catalog # [HBL15FRW](#)



Single Pole Products, Female Receptacle, Double Set Screw Termination, 150 Amp Series, White

Features

- Double Set Screw Termination
- 150 Amp Series
- White

Application

Extra Heavy Duty Industrial

Performance

- Electrical - Amperage Rating - 150A Maximum
- Electrical - Voltage Ratings - 600V AC Maximum
- 250V DC Maximum
- Mechanical - Product Identification - Ratings are a permanent part of device
- Mechanical - Terminal Accommodation - #8 to #2 AWG

General

Catalog Number	HBL15FRW
Color	White
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Male Inlet
Material	Brass/Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	1-Pole
Series	Series 15
Specifications	<ul style="list-style-type: none">• Base Compound - Thermoplastic Elastomer (TPE)• Contact Material - Brass• Mounting Hole - 3x Ø .20"• Retaining Screw Material - Nylon• Termination - (2) 5/32 Socket Head Set Screws
Style	Double Set Screw Female

Type Receptacle, Stud Type
UPC 783585458182

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Amperage Rating 150 A
Connectivity Double Set Screw
Current / Amperage Rating 150 A
Current Rating 150 A
Phase Single Phase
Voltage Rating Description 600V AC/DC
Wattage 90000

Conductor Related

Number Of Wires None
Wire Size #4 AWG Type SC/PPC Wire

Certifications And Compliance

Industry Standard(s)

- National Electric Code (NEC), ANSI/NFPA 70
- UL and cUL Listed
- UL Enclosure Types 3R, 4X, 12

Nema Rating Non-NEMA

Logistics

Carton Quantity 25
Pallet Quantity 4500

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Single Pole Devices](#)
[Specifications - HBL15FRW](#)
[Warranty - Industrial & Commercial Products](#)