



Straight Blade Devices, Female Connector Body, Valise Series, Hospital Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, White, Single Pack



By Hubbell Wiring Device-Kellems
Catalog # [HBL8119V](#)

Valise® Straight Blade Hospital Grade Female Connector 15A, 2-Pole, 3-Wire Grounding, 125V, 5- 15P Nylon.

Features

- Hinged one piece body design for easy assembly
- Powerful, offsetting cord grips clamp on individual conductors

Application

Hospital Grade

General

Color	<ul style="list-style-type: none"> • White • Blanc
Cord Range	0.300"-0.660" (7.6-16.8)
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Insulation	Insulated Body
Item Type	Valise Connector
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2000V AC minimum • Environmental - Flammability - UL 94 HB • Environmental - IP Suitability - IP20 • Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device

Dimensions

Dimensions	2.63 in x 1.25 in x 1.13 in
Display Size	Standard
Height	1.13 in
Length	2.63 in
Weight	0.1 lb
Width	1.25 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Conductor Range	#14 AWG to #12 AWG
Number Of Wires	3-Wire
Wire Size	#16 AWG to #12 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
----------------------	---

Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK L-11 Catalog Page](#)
[Catalog Page - WDK A-36 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Literature - Healthcare Product Solutions](#)

- Mechanical - Terminal Accommodation - #16 to #12 AWG
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

[Literature - Duct Products Guide](#)
[Literature - Emergency Preparedness for Healthcare](#)
[Literature - Healthcare Application Guide](#)
[Literature - Education Application Guide](#)
[Warranty - Industrial & Commercial Products](#)

Temperature Rating

Max Continuous- 75 Degrees C, Minimum- -40 Without Impact

UPC

783585015798



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL8119V-SPEC-EN | REV 1/2024