

Locking Devices, Hubbellock, Industrial, Male Plug, 20A 125V/10A 250V DC/480V AC, 2-Pole 3-Wire Grounding, Non- NEMA, Screw Terminal, Black and White

By Hubbell Wiring Device-Kellems
Catalog # [HBL23005GB](#)



Locking Devices, Hubbellock®, Industrial, Male Plug, 20A, 125V,
2-Pole 3-Wire Grounding, Nylon housing, thermoset interior,
Non- NEMA, Screw Terminal, Black/White

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - 2,000V minimum
- Environmental - Flammability - HB or better
- Environmental - Moisture Resistance - IP30 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #12 AWG stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL23005GB
Color	Black, White
Cord Range	0.320"- .660"(8.12-16.5)
EU RoHS Indicator	Contact Manufacturer
Item Type	20A Hubbellock® Plug
Material	Nylon
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Assembly Screws - Stainless Steel• Contacts - Brass• Cord Clamp Material - Nylon• Device Color - Black/White• Housing - Nylon• Plug Housing - Thermoset

Type	Plugs
UPC	783585017389

Dimensions

Dimensions	1.72 in x 2.31 in x 3.22 in
Height	3.22 in
Length	1.72 in
Weight	0.25 lb
Width	2.31 in

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Cable Range	0.320 - 0.660 in
Number Of Wires	3-Wire

Logistics

Carton Quantity	20
Pallet Quantity	3060

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL23005GB](#)
[Warranty - Industrial & Commercial Products](#)