



Straight Blade Devices, Receptacles, Duplex, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, White, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [HBL8200W](#)



HBL® Extra Heavy Duty MAX Hospital Grade Duplex Flush
Receptacle 15A, 125V, 5-15R.

Features

- Deep body design with circuit ID face
- Patented ground contact provides redundant grounding
- Unique bypass contact design

Application

Extra Heavy Duty Hospital Grade

General

Color	<ul style="list-style-type: none"> • Blanc • Blanc
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 V-0 • Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #14-#10 AWG stranded or solid copper wire only • Mechanical - Terminal Identification - Terminals

Dimensions

Dimensions	3.28 in x 1.65 in x 1.19 in
Display Size	Standard Sized Product
Height	1.19 in
Length	3.28 in
Weight	0.25 lb
Width	1.65 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • CSA Certified, C22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
Nema Rating	5-15R
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK A-9 Catalog Page](#)
[Catalog Page - WDK L-4 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - HBL 8200W AutoCAD Drawing](#)

Identification - Terminals
identified in accordance
with UL 498 and CSA

Series Hospital Grade
Style Thermoplastic Polyester Face
Type • Receptacle
• Receptacle

UPC 783585435688

Engineering Drawing - HBL8200W AutoCAD Drawing
Installation Manuals - WIRING_PD2615_INSTALLINST
Literature - Healthcare Product Solutions
Literature - Duct Products Guide
Literature - Emergency Preparedness for Healthcare
Sales Drawings - WDK_HBL8200_DRAWINGS_PDF
Warranty - Industrial & Commercial Products



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBL8200W-SPEC-EN | REV 1/2024