

HUBBELL

Wiring Device

Switches and Motor Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 100A 600V AC, Stainless Steel, NEMA 4X Enclosure

By Hubbell Wiring Device-Kellems

Catalog # [HBLDS10SSAC](#)

Switches and Motor Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 100A 600V AC, Screw Terminals, Stainless Steel, NEMA 4X Enclosure, With Aux Contact



Features

- Molded-in conduit opening and field installed hub
- Internal frame automatically bonds all grounds
- Reversible interior accommodates top or bottom conduit opening

Application

Labelless

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage, Electrical - Dielectric Voltage - Withstands 3000V AC minimum, Electrical - Max. Working Voltage - 600V AC RMS, Environmental - Flammability - UL94-5VA and V0 Classification, Environmental - Operating Temperature - Max Continuous 75°C, Min Continuous -40°C w/o impact, Environmental - UV Resistance - All materials are UV stabilized, Mechanical - Impact Resistance - In accordance with UL 746C, Mechanical - Mounting - Stainless Steel - Feet are fixed, Mechanical - Product Identification - Identification and ratings are part of external label, Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

Specifications

Standards - RoHS Compliance Status
CM
EU RoHS Indicator
Yes
Industry Standard(s)
UL Listed

Configuration

Mounting Method
Feet are fixed

Current

Amperage Rating
100 A
Dielectric Strength
Withstands 3000V AC minimum
Current Rating
100 A
Phase
Three Phase
Current / Amperage Rating
100 A

Dimensions

Length
11.63 in
Height
5.39 in
Width
7.3 in
Dimensions
11.63 in x 7.3 in x 5.39 in

General

Style
Heavy Duty
Ingress Protection
IP69K
Enclosure Type
Type 4X, IP69k
Series
Non-Fused
Specifications

- Base - #14 Gauge Type 304 Stainless Steel
- Enclosure Gasket - Neoprene
- Handle - Valox®
- Shaft (Unfused) - Valox®
- Top - #14 Gauge Type 304 Stainless Steel

UPC
783585372594
Type
Disconnect Switches

Logistics

Carton Quantity
1

Operational

Operating Temperature
Maximum continuous 75°C and minimum -40°C without Impact

Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)

[Catalog Page \[English\]](#)

[Installation Manual \[Spanish, French, English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved

WDK_CA-HBLDS10SSAC-SPEC-EN | REV 5/2026