



Switches and Motor Controls, Industrial Grade, Disconnect Switches, Unfused Switch, Three Pole, 30A 600V AC, Stainless Steel, NEMA 4X Enclosure

By Hubbell Wiring Device-Kellems
Catalog # [HBLDS3SS](#)



Switches and Motor Controls, Industrial Grade, Disconnect
Switches, Unfused Switch, Three Pole, 30A 600V AC, Screw
Terminals, Stainless Steel, NEMA 4X Enclosure.

Features

- Molded-in conduit opening and field installed hub
- Internal frame automatically bonds all grounds
- Reversible interior accommodates top or bottom conduit opening

Application

Labelless

General

Mounting Method	Feet are fixed
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current & voltage • Electrical - Dielectric Voltage - Withstands 3000V AC minimum • Electrical - Max. Working Voltage - 600V AC RMS • Environmental - Flammability - UL94-5VA and V0 Classification • Environmental - Operating Temperature - Max Continuous 75°C, Min Continuous -40°C w/o impact • Environmental - UV Resistance - All materials are UV stabilized • Mechanical - Impact Resistance - In accordance with UL 746C • Mechanical - Mounting - Stainless Steel - Feet are fixed • Mechanical - Product Identification -

Dimensions

Dimensions	8.38 in x 4.87 in x 5.39 in
Height	5.39 in
Length	8.38 in
Width	4.87 in

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 3000V AC minimum

Certifications and Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Catalog Page - WDK F-7 Catalog Page](#)
- [Catalog Page - WDK F-17 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - HBLDS3SS AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2520_INSTALLINST](#)
- [Literature - Labelless Disconnects](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - Food Processing Guide](#)
- [Literature - Industrial Solutions](#)
- [Literature - Improved Short Circuit Current Ratings \(SCCR\)](#)
- [Literature - Circuit-Lock® Motor Disconnects](#)
- [Literature - Safety Product Guide](#)
- [Literature - Wiring Device Solutions for Strategic Manufacturing Facilities](#)
- [Literature - Safety Product Guide](#)
- [Sales Drawings - M12330](#)
- [Warranty - Industrial & Commercial Products](#)

	Identification and ratings are part of external label
	<ul style="list-style-type: none">• Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions
Series	<ul style="list-style-type: none">• Non-Fused• MotorQuick/LINKOSITY
Style	<ul style="list-style-type: none">• Heavy Duty• Replacement Switches
Type	<ul style="list-style-type: none">• Disconnect Switches• Accessories For LINKOSITY®• Disconnect Switches• Accessories For LINKOSITY®
UPC	783585242736



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-HBLDS3SS-SPEC-EN | REV 1/2024