



# Locking Devices, Twist-Lock®, Elastogrip®, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, L5-15R, Screw Terminal, Water/Dust-Tight Housing



By Hubbell Wiring Device-Kellems  
Catalog # [HBL25W47](#)

Locking Devices, Twist-Lock®, Elastogrip®, Female Connector Body, 15A 125V, 2-Pole 3-Wire Grounding, NEMA L5-15R, Screw Terminal, Yellow, Water/Dust-Tight Housing.

## Features

- Integral weatherproofing shroud seals connection between plug and connector
- Nylon compression nut keeps water and dust from getting into the body around the cord

## Application

Heavy Duty Industrial

## General

Color	Yellow
Cord Range	0.300"-.655"(7.6-16.6)
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	15A Grounding Elastogrip® Connector
Material	Elastomer / Elastomeric
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstand 2,000V minimum</li> <li>• Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.17</li> <li>• Environmental - Moisture Resistance - IP20 Suitability</li> <li>• Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)</li> <li>• Mechanical - Terminal Accommodation - #18 AWG- #10 AWG stranded</li> </ul>

## Dimensions

Dimensions	1.76 in x 1.76 in x 4.03 in
Display Size	Standard
Height	4.03 in
Length	1.76 in
Weight	0.35 lb
Width	1.76 in

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

## Conductor Related

Cable Range	0.300 - 0.655 in
Number Of Wires	3-Wire
Wire Size	#18 AWG to #10 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA C22.2 No.42</li> <li>• Fed.Spec. W-C-596</li> <li>• Listed to UL 498</li> </ul>
----------------------	---

Nema Rating	L6-15R
-------------	--------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Wiring B-13 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2023](#)  
[Warranty - Industrial & Commercial Products](#)

copper wire only.

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

Temperature Rating

Maximum Continuous: 75° C;  
Minimum Continuous: -40° C  
w/o impact, -25° with impact.

Type

- Connector Body
- Connector Body

UPC

783585235912



**A proud member of the Hubbell Family.**

©2024 Hubbell Incorporated. All rights reserved.  
WDK\_MX-HBL25W47-SPEC-EN | REV 1/2024