

Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Gray

By Hubbell Wiring Device-Kellems
Catalog # [HBL2615SW](#)



Locking Devices, Twist-Lock®, Industrial, Flanged Inlet, 30A 125V, 2-Pole 3-Wire Grounding, L5-30P, Screw Terminal, Gray.

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - V0 per UL94 or CSA 22.2 No.0.17
- Environmental - Moisture Resistance - Type 4, 4X, 12, IP66 suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL2615SW
EU RoHS Indicator	Yes
Environmental Conditions	Watertight
Insulation	Insulated Body
Item Type	30A Watertight Safety-Shroud® Flanged Inlet
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> • Assembly Screws - Stainless Steel • Blades - Brass • Housing / Flange - Gray PBT • Mounting Screw - Stainless Steel • Terminal Retainer - Clear polycarbonate • Terminal Screws - #10-32 Brass (Phillips / Slotted / Robertson)
Type	Flanged Inlet

UPC

783585231648

Dimensions

Dimensions	3.75 in x 3.75 in x 2.27 in
Display Size	Standard Sized Product
Height	2.27 in
Length	3.75 in
Weight	0.6 lb
Width	3.75 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Back Wired Screw Terminals
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC

Conductor Related

Number Of Wires	3-Wire
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed, CSA Certified To Type 4, 4X And Type 12
Nema Rating	L5-30P
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - HBL2615SW](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL2615SW-SPEC-EN | REV 10/2024