



Locking Devices, Twist-Lock®, Industrial, Flanged Receptacle, 30A 125V AC, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, White

By Hubbell Wiring Device-Kellems
Catalog # [HBL2616](#)



Locking Devices, Twist-Lock®, Industrial, Flanged Receptacle, 30A 125V AC, 2-Pole 3-Wire Grounding, L5-30R, Screw Terminal, White.

Features

- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws (Slotted, Phillips, Robertson)
- Mounting screws included

Application

Heavy Duty Industrial

General

| | |
|------------------------------|--|
| Environmental Conditions | Indoor Dry Unless Protected By Additional Means |
| Horsepower - Maximum | 2 |
| Item Type | 30A Grounding Insulgrip® Flanged Receptacle |
| Material | Nylon |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| Operating Temperature | Maximum continuous 75°C and minimum -40°C without impact |
| Performance | <ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - V2 or better per UL94/CSA 22.2 No.0.17 • Environmental - Moisture Resistance - IP20 Suitability • Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact) • Mechanical - Terminal Accommodation - #16 AWG - #8 AWG solid or stranded copper wire only. |

Dimensions

| | |
|--------------|-----------------------------|
| Dimensions | 2.88 in x 2.88 in x 2.09 in |
| Display Size | Standard Sized Product |
| Height | 2.09 in |
| Length | 2.88 in |
| Weight | 0.30 lb |
| Width | 2.88 in |

Electrical Ratings

| | |
|----------------------------|----------------------------|
| Amperage Rating | 30 A |
| Connectivity | Back Wired Screw Terminals |
| Current / Amperage Rating | 30 A |
| Current Rating | 30 A |
| Dielectric Strength | Withstands 2,000V minimum |
| Phase | Single Phase |
| Voltage Rating | 125 VAC |
| Voltage Rating Description | 125 VAC |

Conductor Related

| | |
|-----------------|-------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #16 AWG to #8 AWG |

Certifications and Compliance

| | |
|------------------------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none"> • Certified to CSA C22.2 No.42 • Fed.Spec. W-C-596 • Listed to UL 498 |
| Nema Rating | L5-30R |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Warranty - Industrial & Commercial Products](#)

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

Type

- Flanged Receptacle
- Flanged Receptacle

UPC

783585038810



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_MX-HBL2616-SPEC-EN | REV 1/2024