

Straight Blade Devices,
Receptacles, Decorator Duplex,
Commercial Grade, Corrosion
Resistant, Smooth Face, 20A 125V,
2- Pole 3-Wire Grounding, 5-20R.

By Hubbell Wiring Device-Kellems
Catalog # [IG20DRLA](#)



Straight Blade Receptacle, Decorator Duplex, Commercial Grade,
Corrosion Resistant, Smooth Face, 20A 125V, 2-Pole 3-Wire
Grounding, 5-20R, Back and Side Wired

Features

- Triangle marking on face indicates isolated ground
- Aesthetic Style Line® decorator design
- Triple wipe contacts

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 V-2
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	IG20DRLA
EU RoHS Indicator	Yes
Horsepower - Maximum	1
Item Type	Decorator Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Commercial Specification Grade
Specifications	<ul style="list-style-type: none">• Automatic Self-grounding Staple - Stainless steel• Base - Nylon• Face - Nylon• Ground Contacts - Brass• Mounting Screws - Galvanized Steel

	<ul style="list-style-type: none">• Mounting Strap - .040 in. (1) Galvanized steel• Power Contact - .030" (.8) Brass• Terminal Clamp - .062" (1.6) Nickel Plated steel• Terminal Screws - Plated steel
Style	Style Line Decorator
UPC	783585147918

Dimensions

Dimensions	1.29 in x 1.06 in x 3.28 in
Display Size	Standard Sized Product
Height	3.28 in
Length	1.29 in
Weight	0.15 lb
Width	1.06 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA C22.2, No. 42
----------------------	--

	<ul style="list-style-type: none"> Fed. Spec. WC596 NEMA® WD-6 Compliant UL Listed to UL498 File No. E2186 	Catalog Page - WDK M-18 Catalog Page Catalog Page - WDK A-30 Catalog Page Catalogs - WDK Catalog Full 2024 Customer Notices - Prop 65 Notice Engineering Drawing - IG20DRLA AutoCAD Drawing Installation Manuals - WIRING_PD1579_PD2305_INSTALLINST Sales Drawings - WDK_IG20DRLA_DRAWING_PDF Specifications - IG20DRLA Specification Sheet French Specifications - IG20DRLA Specification Sheet Specifications - Wiring IG20DRLA Specification Sheet Warranty - Industrial & Commercial Products
Nema Rating	5-20R	
Logistics		
Carton Quantity	10	
Product Assets		