

HUBBELL
Wiring Device-Kellems

**Locking Devices, Hubbellock,
Industrial, Receptacle, 60A 600V
AC, 3-Pole 4-Wire Grounding, Non
NEMA, Screw Terminal, Cast
Aluminum, Short Housing.**

By Hubbell Wiring Device-Kellems
Catalog # [HBL26410](#)

Locking Devices, Hubbellock®, Industrial, Receptacle, 60A 600V
AC, 3-Pole 4-Wire Grounding, Black phenolic interior with short
aluminum housing and lift cover, Non NEMA, Screw Terminal,
Metallic



General

Application	
Catalog Number	HBL26410
Color	
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	60A Hubbellock® Grounding Receptacle
Material	Aluminum, Cast
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	Electrical - Current Interrupting - Certified for current interrupting at full rated current Electrical - Dielectric Voltage - 2,000V minimum Environmental - Flammability - UL 94 VO Environmental - Moisture Resistance - IP44 Suitability Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact) Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
Type	Receptacle Receptacle
UPC	783585017303

Dimensions

Dimensions	3.5 in x 4.62 in x 3.58 in
Display Size	Standard Sized Product
Height	3.58 in
Length	3.5 in
Weight	1.7 lb
Width	4.62 in

Electrical Ratings

Amperage Rating	60 A
Connectivity	Screw Terminals
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Multi Phase
Voltage Rating	600 V
Voltage Rating Description	600 V

Conductor Related

Number Of Wires	4-Wire
Wire Size	#8 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	Certified to CSA Standard
	Listed to UL Standard

Logistics

Carton Quantity	5
Pallet Quantity	560

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL26410-SPEC-EN | REV 6/2024