

Hospital Grade Surge Suppression
Receptacle, 20A 125V, 5-20R, Gray

By Hubbell Wiring Device-Kellems
Catalog # [IG8362GYSA](#)

Hospital Grade Surge Suppression Receptacle, 20A 125V, 5-20R,
Gray

Features

- High-impact nylon face resists breakage
- Automatic grounding clip attached to bridge
- Power-on indicator light verifies instantly that power is available
- Distinctive surge symbol provides quick visual identification of surge suppression receptacle

Performance

- Electrical - Frequency - 60Hz
- Electrical - Protection Modes - Normal and Common Modes
- Electrical - Response Time - Approximately 5 ns
- Electrical - Transient Suppression - Peak Energy (10 X 100 Qs)
Peak Current (8 X 20 Qs)
- Electrical - Voltage - 120V AC + 10% - 15%
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - 32°F to 140°F (0°C to 60°C)

General

Catalog Number	IG8362GYSA
EU RoHS Indicator	No
Indicator(s) Type	LED and Audible Alarm
Item Type	Surge Protection Receptacles
Material	Composite
Material - Mounting Hardware	Mounting Screws
Operating Temperature	32 Deg F to 140 Deg F (0 Deg C to 60 Deg C)
Outlet	Straight Blade
Response Time	5
Series	Hospital Grade
Specifications	• Base Material - Nylon • Contact Design - Tandem Modified Bypass • Face Material - Nylon • Mounting Screws - Steel-Zinc Plated • Power Contacts - .031" (.8) Brass
Style	Isolated Ground



UPC 783585960470

Dimensions

Display Size Standard

Electrical Ratings

Amperage Rating	20 A
Connectivity	Terminal Screws
Current / Amperage Rating	20 A
Current Rating	20 A
Frequency Rating	60 Hz
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	• CSA Certified to Specification C22.2 No. 42 • Listed to UL Standards 498 Receptacles • UL Listed File E2186
Nema Rating	5-20R

Logistics

Carton Quantity 10

Product Assets

[Catalog Page - WDK M-13 Catalog Page](#)
[Catalog Page - WDK L-16 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - IG8362GYSA AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1152_INSTALLINST](#)
[Literature - Duct Products Guide](#)
[Literature - SpikeShield® Power Quality Surge Protective Devices](#)
[Sales Drawings - WDK_IG8362_DRAWING_PDF](#)
[Specifications - IG8362GYSA Specification Sheet French](#)
[Specifications - IG8362GYSA](#)
[Specifications - IG8362GYSA Specification Sheet English](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK_CA-IG8362GYSA-SPEC-EN | REV 4/2025