

# Signal and Control, Micro Quick, Female Plug, Field Attachable, 5-Pole, .24-.32" Cable Range

By Hubbell Wiring Device-Kellems

Catalog # [MCMS23F9](#)



Signal and Control, Micro Quick, Female Plug, Field Attachable, 5-Pole, .24-.32" Cable Range.

## Features

- Body with high impact design
- Strain relief protects terminations
- Precision wire funnels eliminate stray strands

## General

Application	Quick Connect/Disconnect Signal and Control
Catalog Number	MCMS23F9
EU RoHS Indicator	No
Environmental Conditions	IP67 Ingress Protection
Item Type	Female Straight Plug
Material - Coupling Nut	Aluminum
Material - Insert	PUR/PA
Material - O-Ring	Neoprene
Material - Overmold	PBT
Material - Shell	PBT
Operating Temperature	-40 Deg C to 85 Deg C
Performance	Electrical - Amperage - 4A  Electrical - Maximum Wire Size - #18 AWG  Electrical - Voltage Rating - 250V  Environmental - Moisture Resistance - IP66 Suitability  Environmental - Operating Temperature - -40°C to 90°C
Thread Size	Non-Threaded
UPC	783585192345

## Electrical Ratings

Amperage Rating	4 A
Current / Amperage Rating	4 A
Current Rating	4 A
Voltage Rating	250V kV

## Conductor Related

Cable Size	.24"-.32"
Cable Specification	UL Listed Portable Cord

## Certifications And Compliance

Industry Standard(s)	CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07  UL 2238 and UL50E, File No. E192071
----------------------	---

## Logistics

Carton Quantity	30
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Pulp & Paper Solutions](#)  
[Literature - PULP & PAPER SOLUTIONS](#)  
[Sales Drawings - WDK\\_MCMS23F9\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
WDK\_CA-MCMS23F9-SPEC-EN | REV 6/2024