

Locking Devices, Hubbellock, Industrial, Receptacle, 60A 600V AC, 3-Pole 4-Wire Grounding, Non NEMA, Screw Terminal, Cast Aluminum, Long Housing



By Hubbell Wiring Device-Kellems
Catalog # [HBL26420](#)

Hubbellock® Industrial Receptacle, 60A 600V AC, 3-Pole 4-Wire Grounding phenolic interior with longuminum housing and lift cover, Non NEMA, Screw Terminal, Metallic

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - 2,000V minimum
- Environmental - Flammability - UL 94 V0
- Environmental - Moisture Resistance - IP44 Suitability
- Environmental - Operating Temperatures - Maximum Continuous 75°C, Minimum -40°C (w/o impact)
- Mechanical - Terminal Accommodation - #8 AWG - #4 AWG solid or stranded copper wire only.
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498

General

Catalog Number	HBL26420
Color	Aluminum
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	60A Hubbellock® Grounding Receptacle
Material	Aluminum, Cast
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"> • Contacts / Springs - Copper alloy • Flange Gasket - Neoprene • Housing / Cover - Cast Aluminum • Mounting Screws - Zinc plated steel • Receptacle Interior - Phenolic • Rivet - Aluminum • Spring - Stainless steel • Terminal - Copper

Type
UPC

- Terminal Screws - Stainless steel
- Receptacle
783585017495

Dimensions

Dimensions	3.5 in x 4.32 in x 4.96 in
Display Size	Standard Sized Product
Height	4.96 in
Length	3.5 in
Weight	2.55 lb
Width	4.32 in

Electrical Ratings

Amperage Rating	60 A
Connectivity	Screw Terminals
Current / Amperage Rating	60 A
Current Rating	60 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Multi Phase
Voltage Rating	600 V
Voltage Rating Description	600 V

Conductor Related

Number Of Wires	4-Wire
Wire Size	#8 AWG to #4 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA Standard • Listed to UL Standard
----------------------	--

Logistics

Carton Quantity	5
Pallet Quantity	560

Product Assets

