

Micro-Quick Control Connectors, Male Angled, 3 Wire, Insulation Displacement

By Hubbell Wiring Device-Kellems

Catalog # [MIMA13IDC](#)

Micro-Quick Control Connectors, Male Angled, 3 Wire, Insulation Displacement.



Features

- Strain relief bushing protects terminations
- Wire Guide for virtually toolless termination
- Insulation displacement contacts are made of Copper Alloy

General

Application	Quick Connect/Disconnect Signal and Control
Catalog Number	MIMA13IDC
Color	Black
EU RoHS Indicator	Yes
Item Type	Male Angled In-Line Plug
Performance	Electrical - Amperage - 3A Electrical - Cable Diameters - .160" to .211" Electrical - Voltage Rating - 32V AC/DC Electrical - Wire Range - #22 AWG max. #24 AWG min. Environmental - Ingress Protection - IP66 Suitability Environmental - Operating Temperature - -20°C to 110°C
Temperature Rating	-20 Deg C to 105 Deg C
UPC	783585226705

Dimensions

Diameter Live Part	.67"
--------------------	------

Conductor Related

Conductor Type	Copper
Number of Conductors	3-Pole

Certifications And Compliance

Industry Standard(s)	CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07 UL 2238 and UL50E, File No. E192071
----------------------	---

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Sales Drawings - WDK_MIMA13IDC_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_CA-MIMA13IDC-SPEC-EN | REV 6/2024