

Signal and Control, Micro Quick, Female Plug, Field Attachable, 4-Pole, .16-.24" Cable Range

By Hubbell Wiring Device-Kellems

Catalog # [MIMS15F7](#)



Signal and Control, Micro Quick, Female Plug, Field Attachable, 4-Pole, .16-.24" Cable Range.

Features

- Body with high impact design
- Strain relief protects terminations
- Precision wire funnels eliminate stray strands

General

Application	Quick Connect/Disconnect Signal and Control
Catalog Number	MIMS15F7
EU RoHS Indicator	No
Environmental Conditions	IP67 Ingress Protection
Item Type	Male In-Line Straight Plug
Material - Coupling Nut	Aluminum
Material - Insert	PUR/PA
Material - O-Ring	Neoprene
Material - Overmold	PBT
Material - Shell	PBT
Operating Temperature	-40 Deg C to 85 Deg C
Performance	Electrical - Amperage - 4A Electrical - Maximum Wire Size - #18 AWG Electrical - Voltage Rating - 250V Environmental - Moisture Resistance - IP66 Suitability Environmental - Operating Temperature - -40°C to 90°C
Thread Size	Non-Threaded
UPC	783585192536

Electrical Ratings

Amperage Rating	4 A
Current / Amperage Rating	4 A
Current Rating	4 A
Voltage Rating	250V kV

Conductor Related

Cable Size	.16"- .24"
Cable Specification	UL Listed Portable Cord

Certifications And Compliance

Industry Standard(s)	CSA Certified, C22.2 No. 182.3 and CSA C22.2 No. 94.2-07 UL 2238 and UL50E, File No. E192071
----------------------	---

Logistics

Carton Quantity	30
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Sales Drawings - WDK_MIMS15F7_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_CA-MIMS15F7-SPEC-EN | REV 6/2024