

Locking Devices, Twist-Lock®, Corrosion Resistant Insulgrip® Connector, 30A, 250V AC, 2 Pole, 3 Wire Grounding, NEMA L6-30R, Yellow nylon



By Hubbell Wiring Device-Kellems
Catalog # [HBL26CM23](#)

Locking Devices, Twist-Lock®, Corrosion Resistant Insulgrip® Connector, 30A, 250V AC, 2 Pole, 3 Wire Grounding, NEMA L6-30R, Yellow nylon

Application

Heavy Duty Industrial/Marine

Performance

- Electrical-Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Mechanical - Terminal Accommodation - #16 AWG - #8 AWG stranded copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498
- Environmental - Flammability - HB or better per UL94/CSA 22.2 No.0.6
- Environmental - Operating Temperatures - Maximum Continuous 75°C
- Minimum -40°C (w/o impact)
- Environmental - Moisture Resistance - IP20 Suitability

General

Catalog Number	HBL26CM23
Color	Yellow
Cord Range	0.360"-0.930" (9-24)
EU RoHS Indicator	Yes
Environmental Conditions	Corrosion Resistant
Insulation	Insulated Body
Item Type	30A Corrosion Resistant Insulgrip® Connector
Listings	<ul style="list-style-type: none">• UL 498• Fed.Spec. W-C-596• CSA C22.2 No.42
Material	Nylon
Material - Mounting Hardware	Cord Mounted
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none">• Assembly Screws - Steel - nickel plated

- Contacts - Nickel Plated Brass
- Housing / Cord Clamp - Nylon
- Terminal Clamp - Cold rolled steel - nickel plated
- Terminal Retainer - Clear polycarbonate
- Terminal Screws - #10-32 Bronze (Phillips / Slotted / Robertson)

UPC

783585039121

Dimensions

Dimensions	3.86 in x 2.26 in x 2.26 in
Display Size	Standard
Height	2.26 in
Length	3.86 in
Weight	0.35 lb
Width	2.26 in

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	30 A
Current Rating	30 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	250 VAC
Voltage Rating Description	250 VAC

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#16 AWG to #8 AWG

Certifications And Compliance

Industry Standard(s)

- Certified to CSA C22.2 No.42
- Fed.Spec. W-C-596
- Listed to UL 498

Nema Rating

L6-30R

Standards - RoHS Compliance Status

CM

Logistics

Carton Quantity 30

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Specifications - HBL26CM23](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-HBL26CM23-SPEC-EN | REV 10/2024