

Spider Portable Power, Complete Unit,
Locking Style, With 6) 20A 125V
Receptacles- 1) 30A 250V Locking
Receptacle- 1) 50A 125/250V Inlet and
Outlet

By Hubbell Wiring Device-Kellems
Catalog # [SBTL2](#)

Temporary Power Products, Spider Portable Power, Complete
Unit, Locking Style, With 6) 20A 125V Receptacles- 1) 30A 250V
Locking Receptacle- 1) 50A 125/250V Inlet and Outlet, Yellow

Features

- Individual GFCI modules
- TYPE 3R metallic enclosure and heavy duty,abuse resistant legs
- Standard stab termination circuit breakers with gasketed lift cover

Application

Heavy Duty Portable

Performance

Environment - Moisture Resistance - Indoor and outdoor wet and dry locations

Specifications

Environmental Conditions	Indoor and Outdoor
EU RoHS Indicator	No
Nema Rating	6) L5-20R, 1) L6-30R, 1) 50A Non-NEMA In/Out
Industry Standard(s)	UL 1640 cUL and CSA, UL 943

Conductor

Number Of Wires	4-Wire Grounding
Wire Size	#10 AWG Min #6 AWG Max
Number Of Poles	3-Pole

Current

Amperage Rating	50 A
Voltage Rating Description	120/240 VAC



Current Rating	50 A
Voltage Rating	120/240 VAC
Wattage	12500
Connectivity	Pre-Wired
Phase	Single Phase
Current / Amperage Rating	50 A

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

Color	Yellow
Series	Spider II
Specifications	• Code Compliance - NEC®, ANSI/NFPA 70 • Enclosure Type - 3R, rainproof, suitable for use in damp locations
UPC	783585369518
Type	Locking Style 6-20A, 125V, 1-30A, 250V , 1-50A 125/250V Inlet and Outlet Yellow
Material - Mounting Hardware	Non-Mounted, Portable
Item Type	Twist-Lock® Singles
Material	Thermoplastic

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)